

INDOT-Industry Preseason Update - All Districts Webinar

April 20, 2022

Questions & Answers

Aggregate Session:

Q: Will INDOT be utilizing 43 in upcoming projects?

A: At this time, INDOT is not aware of any plans to use or specify #43 size aggregates. I would suggest contacting Greenfield District to see if they are aware of any contracts that spec a #43.

Q: If my name has changed due to marriage, do I need to let anyone know for CAPP?

A: Please contact someone at your district to update your information.

HMA Session:

Q: For the auto extractors, do sample weights follow AASHTO/ASTM or ITM guidelines? Currently ITM 571 requires 4000 grams for a 25mm, however AASHTO/ASTM allows for 3000 grams. Most auto extractors have a sample size maximum of 3500 grams.

A: For sampling and sample prep, ITM 571 governs over the ASTM. Even with the centrifuge extractors we split the 4000g samples into 2 samples of 2000g. We will be doing the same thing for the auto extractors.

Mix Size	Minimum Weight of Sample	Mix Size	Minimum Weight of Sample
4.75 mm	1000 grams	19.0 mm	3000 grams
9.5 mm	1500 grams	25.0 mm	4000 grams Split in 2 samples
12.5 mm	2000 grams		